

Garant

Arbor for screw-in milling cutters with thread vibration-damped, tapered form, HSK-A 63, Thread M×length L1: M16X200



Order data

Order number	307037 M16X200
GTIN	4045197905154
Item class	31A

Description

Version:

With RFID/Balluffchip bore. Tapered design. **Vibration damped version, arbor with vibration-damping core.**

Application:

To take screw-in milling cutters with thread.

Optional extras:

Extensions No. 301342, reducers No. 301344, coolant tube No. 309880, coolant tube socket wrench No. 309890.

Note:

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

Technical description

External \varnothing D	45 mm
Thread M	M16×200
\varnothing D ₂	29 mm
L ₂	5 mm
Bore \varnothing D ₁	17 mm
Overhang dimension A	226 mm

Reach L ₁	200 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Vibration	damped
Type of product	Threaded copy mill arbor