

**Clamping head soft, SK 100, Initial bore  $\varnothing$ : 65mm****Order data**

Order number	329956 65
GTIN	2050001925978
Item class	33H

**Description****Version:**

Soft (reduced hardness of 40 HRC in the bore) for boring out.

Clamping heads, **round profile, in 0.5 mm or 1 mm increments. Please specify the required clamping  $\varnothing$  when ordering.**

**Application:**

Versatile application range, machining centres, measuring machines or pallet clamping.

**Note:**

Other taper sizes and shapes (e.g. square) and machinable blanks **on request!**

**Clamping heads for special profiles to your individual requirements on request.**

**Technical description**

Initial bore $\varnothing$	65 mm
Hardness	60 HR
Profile	round
Length L	59 mm
Adapter	SK 100

Type of product

Clamping head