

**Load cell, Measuring range: 0-0,25kN****Order data**

Order number	479100 0-0,25
GTIN	2050001056214
Item class	47F

**Description****Version:**

Hydraulic load cell with directly attached pressure gauge for static and quasi-static force measurement.

Body and piston stainless steel, pressure gauge of pressed brass with memory pointer. Protected against contamination with foreign particles and water spray (IP43).

3×M5 tapped hole in the cell base for attachment.

**Advantage:**

When used in accordance with instructions, a leaktightness warranty of 5 years is given.

**Function:**

IP43: Protected against splashed water from directions up to 60° relative to normal operating position and protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away.

**Application:**

In machine tool building.

**Supplied with:**

Display unit, manufacturer's certificate of conformity, and transport case.

**Technical description**

Measuring range	0 - 0.25 kN
Piston area	10 cm <sup>2</sup>
Height of load cell	30 mm
Scale graduations	0.01 kN
Ø load cell	75 mm
Operating temperature	-10 - 50 °C
Error limit	±1.6 of the full scale value (±2.5 with memory pointer) %
Piston Ø	45 mm
IP Index of Protection	IP 43
Measurement technology	analogue
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Type of product	Load cell