

3M**Velour-backed abrasive disc 237AA (A), Ø 125 mm, Grit: 120****Order data**

| | |
|--------------|---------------|
| Order number | 567726 120 |
| GTIN | 2050001711519 |
| Item class | 53M |

Description**Version:**

The **back of the disc is covered with velour loops** which are self-attaching to **hook and loop fastener backing pads**, e.g. No. **567760** . For quick disc changing.

237AA Trizact™ with fine-structured pyramidal surface of micro-Aluminium Oxide mineral particles (A).

Application:

On **angle grinders** / eccentric grinders with hook and loop fastener pads (dust removal not available). Maximum working speed **40 m/s**.

For a **fine and uniform surface finish** all steels, stainless steels, brass and titanium alloys. Specially for contour grinding and preparation for polishing.

Note:

Suitable hand sanding block for hook and loop grinding discs see No. 567857 size 125 and Gr.150. See No. 566902 – 566950 for velour abrasive discs. For mini grinding systems Ø 50 mm and Ø 75 mm, see No. 554005 onwards.

Technical description

| | |
|------|-----|
| Grit | 120 |
|------|-----|

| | |
|---|---------------------------------------|
| 3M grit designation | A160 |
| Disc Ø | 125 mm |
| Manufacturer's designation | 237AA Trizact™ |
| Series | 237AA |
| Grinding media | Aluminium oxide mineral particles (A) |
| Grinding medium code | A |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 125 mm |
| Propulsive equipment | Angle grinder |
| maximum circumferential speed | 40 m/s |
| Type of product | Velour-backed abrasive disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------|----------------|----------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| dry | suitable | | |

Accessories

| | |
|---|------------|
| Hook and loop polishing pad,M14 External Ø 125 mm | 567762 125 |
| Hook and loop backing pad,M14 External Ø 125 mm | 567760 125 |
| | 567857 125 |

Hand sanding block with hook and loop fastening suitable
for disc Ø 125 mm
