



Burr Z3 – medium with chip breaker, HSS, Type: NS1230



Order data

Order number	541200 NS1230
GTIN	4045197156327
Item class	52D

Description

Version:

Special shapes: E, NS, K.

Shank \varnothing 6 mm. **Special shape NS angle with end cut** (WKNS).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Note:

Reduced speed for burrs with an overall length of 120 mm: maximum 11,000 rpm

Technical description

Head \varnothing	12 mm
Shape description	Angle with end cut
Angle	8 degrees
Shape	NS1230
Overall length	70 mm
Shank \varnothing	6 mm
Tooth type abbreviation	Z3
Type of cut	with chip breaker
Toothing grit designation	medium
Head length	30 mm
Series	Tooth configuration Z3

Tool material	HSS
Type of product	Burr