

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 10/07mm**

**Order data**

Order number	260320 10/07
GTIN	4045197877697
Item class	21T

**Technical description**

Clamping height $L_2$	9.6 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Centre offset $L_3$	7 mm
Overall length $L$	125 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Setting angle $\kappa$	107.5 degrees
ISO code toolholder	E10K SDQCR/L07
Pack of insert screws	269028 7
Shank $\varnothing D_s$	10 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500