

KERN**Hanging scales type CH, maximum weighing range: 50Pkg****Order data**

Order number	479430 50P
GTIN	4045761027190
Item class	47D

Description**Version:**

- **Simple operation with 3 buttons.**
- **With tare button, attach empty container and set indication to zero.**
- **Hold button, the indication can be frozen for 5 seconds.**
- **Display unit switchable between kg, N and lb.**

Supplied with:

1 battery No. 081561 size 6LR61.

Technical description

Scale divisions	50 g
Body height	176.5 mm
maximum weighing range	0 - 50 kg
Net weight	0.35 kg
Body width	90 mm
Body depth	30 mm

Calibration	K2
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Manufacturer's designation	CH
Type of product	Suspended scales / crane scales

Services

CalibrationScales maximum weighing range 50 kg	027700 50
--	-----------