

**Garant**
**Jobber drill, long, HSS-E N, uncoated, Ø DC h8: 10,2mm**

**Order data**

Order number	116065 10,2
GTIN	4045197270801
Item class	11B

**Description**
**Version:**

Profile ground. Standard core thickness and core taper. Bright finish.  
With point geometry shape AC from 2 mm.

**Advantage:**

For drilling with drill bushes or long reach applications.  
For high-tensile tempered steels, **including TOOLOX.**

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

**Note:**

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability

**Technical description**

Flute length $L_c$	121 mm
Feed $f$ in steel $< 1100 \text{ N/mm}^2$	0.08 mm/rev.
Number of cutting edges $Z$	2
Nominal $\varnothing D_c$	10.2 mm
Tolerance nominal $\varnothing$	h8
Shank $\varnothing D_s$	10.2 mm
Overall length $L$	184 mm
Standard	DIN 340
recommended maximum drilling depth $L_2$	105.7 mm

Point angle	118 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS E
Type	N
Helix angle	35-40 degrees
Through-coolant	no
Colour ring	red
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	10 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	8 m/min	P
TOOLOX 33	suitable	8 m/min	H
TOOLOX 44	suitable	5 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	12 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	M
CuZn	suitable only under restricted conditions	80 m/min	N
Oil	suitable		
wet maximum	suitable		