

Garant
Machine tap for wire thread inserts HSS-E-PM, TiCN, EG-M: EG-M8

Order data

Order number	138200 EG-M8
GTIN	4045197866943
Item class	11H

Description
Version:

Tap to **DIN 40435** (similar to DIN 371 / DIN 376).

Achieves outstanding tool life, due to high-quality substrate and TiCN coating. For wide application range of different materials.

Application:

For production of AC mounting thread to metric ISO threads **DIN 8140** for **STI** (Screw Thread Insert) wire thread inserts.

Note:

Please ensure without fail to state the correct **tapping drill Ø (see table)!**

Tool material: HSS E PM

Standard: DIN 40435

Tolerance class: 6H mod.

Thread pitch: 1.25 mm

Overall length L: 100 mm

Shank Ø D_s: 10 mm

Shank square □: 8 mm

Tapping hole Ø: 8.4 mm

Technical description

Shank Ø D _s	10 mm
Tolerance class	6H mod.
Thread pitch	1.25 mm
Number of clamping slots	3
Tapping hole Ø	8.4 mm

Thread Ø	8 mm
Standard	DIN 40435
Shank square □	8 mm
Number of cutting edges Z	3
Overall length L	100 mm
Tool material	HSS E PM
Thread depth	24 mm
Thread size	M8
Coating	TiCN
Thread type	EG-M
Flank angle	60 degrees
Taper lead form	E
Helix angle	45 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap