


HOLEX Pro INOX solid carbide milling cutter HPC, AlCrN, Ø e8 DC: 8mm

Order data

Order number	202382 8
GTIN	4045197879608
Item class	12X

Description
Version:

HPC milling cutter with **newly developed high-performance coating** for **outstanding tool life** and **optimum metal removal rate** in a wide range of stainless steels.

Can be used at **high cutting speeds**, highly suitable even for steels up to approx. 1100 N/mm².

Technical description

Shank Ø D _s	8 mm
Recess Ø D ₁	7.7 mm
Overall length L	68 mm
Corner chamfer width at 45°	0.2 mm
Shank	DIN 6535 HB to h6
No. of teeth Z	3
Feed f _z for side milling in INOX > 900 N/mm ²	0.04 mm
Tolerance nominal Ø	e8
Cutting edge Ø D _c	8 mm
Overhang length L ₁ incl. recess	30 mm
Feed f _z for slot milling in stainless steel > 900 N/mm ²	0.025 mm
Flute length L _c	24 mm
Direction of infeed	horizontal, oblique and vertical

Helix angle	35 degrees
Corner chamfer angle	45 degrees
Series	Pro Inox
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	215 m/min	P
Steel < 750 N/mm ²	suitable	200 m/min	P
Steel < 900 N/mm ²	suitable	160 m/min	P
Steel < 1100 N/mm ²	suitable	160 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	135 m/min	P
TOOLOX 33	suitable only under restricted conditions	100 m/min	H
TOOLOX 44	suitable only under restricted conditions	70 m/min	H
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	75 m/min	M

Uni	suitable only under restricted conditions
wet maximum	suitable
wet minimum	Suitable
dry	Suitable only under restricted conditions
Air	Suitable only under restricted conditions