

KERN**Platform scales, type EOB, maximum weighing range: 35kg**

Order data

Order number	479600 35
GTIN	4045761192157
Item class	47D

Description

Version:

- **Robust parcel scales for the dispatch department.**
- **Very simple operation with four buttons.**
- **Display unit with numeral height 25 mm can be placed away from the platform; can be positioned or mounted using the flexible cable approx. 2 m long.**
- **Suitable for mains and battery operation, auto-off after 3minutes.**

Supplied with:

Mains adapter and wall bracket for display unit.

Optional extras:

6 batteries No. 081561 size LR6, stand for the display unit available on request.

Technical description

Display unit width	215 mm
Scale divisions	10 g
Display unit height	50 mm
maximum weighing range	0 - 35 kg
Dimensions of weighing plate	315×305 mm

Reproducibility	10 g
Display unit depth	110 mm
Net weight	3.8 kg
Manufacturer's designation	EOB
Calibration	K2
Power supply	Battery-powered
Number of batteries contained	6
Article no of the battery / rechargeable battery fitted	081561 LR6
Number height display unit	25 mm
Type of product	Platform balance

Services

CalibrationScales maximum weighing range 50 kg	027700 50
DAkkS calibrationScales maximum weighing range 50	027710 50

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------