



## Double ratchet ring spanner, Widths across flats: 12X14mm



### Order data

Order number	614843 12X14
GTIN	4045197879455
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths. Reversible for left- and right-hand tightening, plus centre position. With unequal jaw widths, deep cranked. Extremely small working arc of 5°.

#### Material:

Chrome vanadium steel, matt chrome-plated.

### Technical description

overall length L	218 mm
Width across flats 1	12 mm
maximum ring height h <sub>2</sub>	20.5 mm
Width across flats	metric
maximum ring Ø D1	24 mm
maximum ring Ø D2	28 mm
maximum ring height h <sub>1</sub>	18 mm
Width across flats 2	14 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Ring end cranked	yes
Ratchet reversible	no
Type of product	Spanner