



## Double ratchet ring spanner, Widths across flats: 13X15mm



### Order data

Order number	614843 13X15
GTIN	4045197879462
Item class	62A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths. Reversible for left- and right-hand tightening, plus centre position. With unequal jaw widths, deep cranked. Extremely small working arc of 5°.

#### Material:

Chrome vanadium steel, matt chrome-plated.

### Technical description

Width across flats	metric
Width across flats 1	13 mm
maximum ring $\varnothing$ D2	31 mm
overall length L	238 mm
maximum ring $\varnothing$ D1	28 mm
maximum ring height $h_1$	20 mm
Width across flats 2	15 mm
maximum ring height $h_2$	21.5 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Ring end cranked	yes
Ratchet reversible	no
Type of product	Spanner