



Safety coupling with external thread, External thread connection: 3/8in



Order data

| | |
|--------------|---------------|
| Order number | 080321 3/8 |
| GTIN | 7391390295446 |
| Item class | 08A |

Description

Version:

The eSafe safety coupling satisfies the ISO standard 4414 and EN 983. First it is vented; uncoupling is then performed as a second step (no whiplash).

Flow rate: 4000 ltr / min, maximum operating pressure 16 bar

Material: galvanised steel / brass

Steel couplings have many advantages in pneumatic systems compared to standard brass couplings:

- **Easy to use with only one hand with low coupling force.**
- **High flow rates as a consequence of very low pressure drop.**
- **Long working life due to surface treatment and hardened components with tight manufacturing tolerances.**
- **Cost-effectiveness – the amortisation time is 2 years at the most.**

Application:

For improving the performance, economics and safety of industrial compressed air installations with low coupling force combined with a compact and easy to grasp design.

Note:

Compressed air safety coupling CEJN series 410 eSafe (with venting function) satisfies the European standard 10.4 (nominal Ø 10.4 mm) flow rate up to 4000 ltr/min.

Technical description

| | |
|----------------------------|------------|
| maximum operating pressure | 16 bar |
| Flow rate | 4000 l/min |
| Connection external thread | 3/8 in |
| Series | 410 |
| Type of product | Coupling |