

Garant
Burr Z9 very coarse (NF/Alu), Carbide, Type: F1630

Order data

Order number	540709 F1630
GTIN	4045197522542
Item class	51D

Description
Version:

Shank Ø 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round arch shape F** (RBF).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Shank Ø: 6 mm

Shape description: round arch

Head Ø: 16 mm

Head length: 30 mm

Overall length: 70 mm

Shank Ø: 6 mm

Technical description

Overall length	70 mm
Shape	F1630
Shape description	round arch
Toothing grit designation	very coarse (NF/Alu)
Head Ø	16 mm
Tooth type abbreviation	Z9

Shank Ø	6 mm
Head length	30 mm
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		