

Gap gauge, Type: E



Order data

Order number	484223 E
GTIN	2050001936943
Item class	48B

Description

Version:

Double-ended gap gauge with intermediate size and ISO tolerance class, e.g. **No. 484223 size 15.8 m6** or numerical tolerance e.g. No. 484223 **size 41.04 + 0.01/ -0.02**

Double-sided gap gauge of first class gauge steel, hardened, stress-relieved, ground, and lapped. "Go" end with **wear allowance** to DIN 7163.

Application:

For testing shafts for clearance, transition or interference fits.

Standard:

Toleranzen und Abmaße nach **DIN EN ISO 1938-1** und **DIN 7163**.

Technical description

Type of gauge	"Go" plug gauge
Type of gauge	"No Go" gauge
Standard	DIN 7164
Standard	DIN 7150-2
Standard	DIN 7163
Tolerance zone	b
Tolerance zone	c

Tolerance zone	a
Tolerance zone	ef
Tolerance zone	e
Tolerance zone	cd
Tolerance zone	d
Tolerance zone	fg
Tolerance zone	g
Tolerance zone	f
Tolerance zone	js
Tolerance zone	k
Tolerance zone	h
Tolerance zone	j
Tolerance zone	n
Tolerance zone	p
Tolerance zone	m
Tolerance zone	t
Tolerance zone	u
Tolerance zone	r
Tolerance zone	s
Tolerance zone	x
Tolerance zone	y
Tolerance zone	v
Tolerance zone	zb
Tolerance zone	zc
Tolerance zone	z
Tolerance zone	za
Quality	10
Quality	11
Quality	9

Quality	12
Quality	7
Quality	13
Quality	8
Quality	6
Nominal size	15 - 18.999 mm
Material	Gauge steel
Calibration	L8
Type of product	Gap gauge

Services

CalibrationGap gauge maximum nominal size 50 mm	028700 50
DAkkS calibrationGap gauge maximum nominal size 5-100 mm	028710 5-100