

KERN**Platform scales, type EOB, maximum weighing range: 300Lkg**

Order data

Order number	479600 300L
GTIN	4045761192096
Item class	47D

Description

Version:

- **Robust parcel scales for the dispatch department.**
- **Very simple operation with four buttons.**
- **Display unit with numeral height 25 mm can be placed away from the platform; can be positioned or mounted using the flexible cable approx. 2 m long.**
- **Suitable for mains and battery operation, auto-off after 3minutes.**

Supplied with:

Mains adapter and wall bracket for display unit.

Optional extras:

6 batteries No. 081561 size LR6, stand for the display unit available on request.

Technical description

Scale divisions	100 g
Display unit width	215 mm
Dimensions of weighing plate	950×500 mm
Display unit height	50 mm
Display unit depth	110 mm

Net weight	17 kg
Manufacturer's designation	EOB
Reproducibility	100 g
maximum weighing range	0 - 300 kg
Calibration	Price on request
Power supply	Battery-powered
Number of batteries contained	6
Article no of the battery / rechargeable battery fitted	081561 LR6
Number height display unit	25 mm
Type of product	Platform balance

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------