



### Precision scales, type PCB, maximum weighing range: 10000g



#### Order data

Order number	479510 10000
GTIN	4045761094215
Item class	47D

#### Description

##### Version:

- **Selectable mains and battery operation. Attention: German version! Please order a GB adapter plug No. 08 1174\_GB separately. Auto-off after 3 minutes.**
- **CAL calibration programme: For accuracy adjustment (required external calibration weight available on request).**
- **Quantity counting: Reference quantities selectable 5, 10, 25, 50 pieces. Display selectable between pieces and weight.**
- **Formulation weighing: Separate memory for weight of the tare vessel and of the formulation ingredients (net totals).**

##### Supplied with:

Mains adapter 230 V/ 50 Hz and protective hood.

##### Optional extras:

Battery No. 081561 size 6LR61; internal rechargeable battery on request. Data cable, printer on request.

#### Technical description

Reproducibility	0.1 g
Scale divisions	0.1 g

## Data sheet

Dimensions of weighing plate	150×170 mm
Height	79 mm
maximum weighing range	0 - 10000 g
Linearity	± 0.3 g
Manufacturer's designation	PCB
Net weight	2 kg
Settling time	3 s
Depth	245 mm
Minimum unit weight	2 g
Width	163 mm
Power supply	Rechargeable battery-powered
Power supply	Battery-powered
Interface	RS232 interface
Calibration	K2
Type of product	Precision balance

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/479510-10000>