

Garant**Slot cutting insert without chamfer C11, TiN, for slot width m: 4mm****Order data**

Order number	290379 4
GTIN	4045197881984
Item class	29L

Description**Version:**

With TiN coating.

Suitable for regrinding.

Application:

For producing slots according to DIN 6885, DIN 138 and factory standards.

For slot widths with tolerance JS9, use cutter inserts with tolerance H7.

Note:

- **Special sizes (slot widths) available on request.**
- **Detailed application values can be found in our application ToolScout.**

From slot width 16 mm it is essential to perform two passes. The first pass must be performed for approx. half the slot width (e.g. 10 mm for a desired slot width of 18 mm).

Technical description

Blade width w	4.145 mm
for slot width m	4 mm
Tip thickness b	7 mm

Groove depth t	2.6 mm
Tool material	HSS
Coating	TiN
for precision fit	C11
Type of product	Keyway broaching and profile slotting tool

User data

	Suitability	V _c	ISO code
Alu plastics	suitable		
Aluminium (short chipping)	suitable		
Alu > 10% Si	suitable		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable only under restricted conditions		
INOX < 900 N/mm ²	suitable		
INOX > 900 N/mm ²	suitable only under restricted conditions		
Ti > 850 N/mm ²	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Graphite, GRP, CRP	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		

