

Garant**Slim hydraulic chuck, SK 40 A = 200, Clamping range Ø D1: 10mm****Order data**

Order number	302096 10
GTIN	4045197868688
Item class	31A

Description**Version:**

- **Extremely slim design (3° contour)**
- **Processed surface structure.**
- **With RFID/Balluffchip bore.**
- **Axial length adjustment possible.**
- **Shanks hard turned.**
- **Reducing adapters can be used.**

Application:

Especially for tool and mould making. **Wherever reduced interference contours are required.**
For drilling, reaming, and milling. For clamping tools with shank tolerance h6.

Supplied with:

Hexagon socket drive with T-handle.

Optional extras:

Pull studs (AB) No. 308600 – 308806, AB pull stud wrenches No. 308820 / 308835, Reducing sleeves No. 302135 – 302187.

Technical description

Overhang dimension A	200 mm
L ₂	162 mm
External Ø D	49.5 mm
Ø D ₃	41.4 mm
Clamping Ø D ₁	10 mm

Ø D ₂	20 mm
Adapter	SK 40 A = 200
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Balluffchip bore	yes
Type of product	Hydraulic clamping chuck

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/302096-10>