

**Garant**
**Short drill chuck Form ADB, BT 40, Clamping range: 0,3-10mm**

**Order data**

Order number	303175 0,3-10
GTIN	4045197868794
Item class	31B

**Description**
**Version:**

For clockwise and anticlockwise rotation.

Concentricity  $\leq 20 \mu\text{m}$ .

With through coolant feed up to max. 50 bar. Max. slim design for the most popular  $\varnothing$  up to 10.2 mm.

**Supplied with:**

**Clamping wrench.**

**Optional extras:**

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Clamping range	0.3 - 10.2 mm
Spare chuck key No. 627425	4 AF
Overhang dimension A	73 mm
External $\varnothing$ D	38 mm
Adapter	BT 40
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	ADB

Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 µm
Type of product	Short drill chuck

## Accessories

Pull stud 60°sealed suitable for steep tapers 40	308785 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 45°sealed suitable for steep tapers 40	308765 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Hexagon screwdriver, with T-handle Hexagon 4 mm	627481 4
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40