

Garant
Short drill chuck Form A, HSK-A 63, Clamping range: 0,3-10mm

Order data

Order number	307682 0,3-10
GTIN	4045197868800
Item class	31B

Description
Version:

- For clockwise and anticlockwise rotation.
- With RFID/Balluffchip bore.

With through coolant feed up to max. 50 bar.
Concentricity $\leq 20 \mu\text{m}$. Concentricity $\leq 20 \mu\text{m}$.

Supplied with:

Clamping wrench with T-handle.

Optional extras:

Socket wrench No. 309890. Coolant tube No. 309880.

Technical description

Spare chuck key No. 627425	4 AF
Overhang dimension A	96.5 mm
Clamping range	0.3 - 10.2 mm
Type	slim
External \varnothing D	38 mm
Adapter	HSK-A 63
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-7

Arbor standard	DIN 69893-1
Shape	A
Through-coolant	yes, with max. 50 bar
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 20 µm
Type of product	Short drill chuck

Accessories

Hexagon screwdriver, with T-handle Hexagon 4 mm	627481 4
---	----------