

Garant
HiPer-Drill base body, 10×D, Ø DC: 26mm

Order data

| | |
|--------------|---------------|
| Order number | 231617 26 |
| GTIN | 4045197869074 |
| Item class | 21S |

Description
Version:

- **Very high feed rates and maximum performance due to optimally matched geometries and materials.**
- **Precise positioning of the cutter insert due to Vee insert seating and secure clamping by the centre bore.**
- **High concentricity when assembled.**
- **Shank support for optimum stability in operation.**

Polished flutes.

Application:

For stationary and rotating use. For holes up to IT9 accuracy.

Note:

Clamp in a hydraulic chuck (such as No. 302026 size 20) for optimum radial run-out.

For optimum stability, clamp the drill so the overhang is as short as possible.

Further sizes up to Ø 50.99 mm available on request.

The insert screw must be replaced after every fifth change of cutter insert.

Reduce feed rates f by 10 % and v_c values by 30 %.

For process reliability when using the drill, initial pilot drilling to 1.5×D with the drill No. 231600 with the same cutter insert size and type is necessary. **The generation of a pilot hole improves process reliability.**

Technical description

| | |
|--------------------|----------------------|
| Shank Ø D_s | 32 mm |
| Shank length L_s | 60 mm |
| Dia. range D_c | 26 - 26.99 mm |
| Clamping screw | 231999 10IP (3.3 Nm) |

| | |
|---------------------------|------------------------------------|
| Reach L ₁ | 270 mm |
| Series | HiPer-Drill |
| Number of cutting edges Z | 2 |
| Overall length L | 368 mm |
| Version | 10xD |
| Shank | ISO 9766 |
| Use for drilling | limited drilling through a stack |
| Use for drilling | limited drilling with oblique exit |
| Use for drilling | limited cross-drilling |
| Use for drilling | limited oblique spot drilling |
| Through-coolant | yes |
| Type of product | Indexable drill |

Accessories

| | |
|---|-------------|
| PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP | 674252 15IP |
| Torque screwdriver, fixed setting set torque 5,0 N·m | 211750 5,0 |
| Torx Plus® screw Drive 15IP | 231999 15IP |