



Torque screwdriver with scale, to take D 6.3 bits, ESD, maximum torque: 200cNm



Order data

Order number	659917 200
GTIN	7610733269464
Item class	63D

Description

Version:

Power grip with non-allergenic elastomer coating allows transmission of the required torque with no problems even with **wet or oily hands**. On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use. The release torque is higher than the tightening torque (overload protection).

Suitable for ESD work.

The desired torque is set using an adjustment wheel at the end of the handle. Putting the wheel into the locked position prevents inadvertent changes to the setting. Easy to read micrometer scale, protected against dirt.

Bit holder with magnet to take C 6.3 bits.

Application:

For controlled tightening of screws to a pre-set torque.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Scale graduation, 1 graduation =	5 cNm
Display	analogue
Torque measuring accuracy	±6 %
Torque range	0.4 - 2 Nm

maximum torque	200 cNm
Torque range	40 - 200 cNm
Bit socket	D 6,3
Trigger principle	mechanical slip clutch
Adjustable trigger value	adjustable
Setting the trigger value	with adjustment scale
Feedback	triggering
Standard	DIN EN ISO 6789
Measurement process	Torque
Overall length L	144 mm
Connection format	Bit holder 1/4 inch
Reversible reading	Nm
Weight	113 g
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Manufacturer's designation	MecaTorque ESD
electrostatic characteristic	EGB/ESD
Torque fixed setting	no
Type of product	Torque screwdriver

Services

Calibration Torque screwdriver maximum torque 0,04-20 N·m

020200 0,04-20

Accessories

Electronic torque screwdriver tester "TST" maximum torque
2 N·m

654300 2

Electronic torque screwdriver tester "TST" maximum torque
10 N·m

654300 10