

Garant
Self-tightening high-performance drill chuck with MT shank, MT shank: 3

Order data

Order number	341122 3
GTIN	4045197880741
Item class	31K

Description
Version:

High performance precision three-jaw drill chucks. High concentricity, keyless, self-tightening, high clamping force. Easily released by hand. Wearing parts hardened and exchangeable.

- **Drill chuck and MT shank are a single unit.**
- **High concentricity, optimum stability.**
- **Easy and quick change due to short design, advantageous for confined working areas.**

Application:

For bench and pillar drilling machines, milling machines, lathes, for use with arbors No. 342300 – 342850 or directly on machine spindles.

Standard:
DIN 238
Note:

The self-tightening effect works only for clockwise rotation.

Technical description

External Ø	50 mm
L ₁ closed	97.5 mm
Clamping range	1 - 13 mm
L ₁ open	85 mm
Type of product	Drill chuck keyless

