

**Garant**
**Face mill arbor with cooling channel bores, PSC 80 short, Spigot  $\varnothing$  d1: 40mm**

**Order data**

Order number	308551 40
GTIN	4045197870728
Item class	31C

**Description**
**Version:**

- With RFID/Balluffchip bore.
- All shanks hard turned (for smooth running!).
- Mating faces of the PSC internal contour machined.

**Application:**

For holding shell end mills and face mills with cross keyway.

**Supplied with:**

Lock screw.

**Optional extras:**

Toggle spanner No. 309840, cutter lock screw No. 309860.

Coolant tube and assembling key for coolant tubes No. 309885; 309893.

**Technical description**

Spare milling cutter lock screw No. 309860 / 309861	40
Overhang dimension A	60 mm
Spigot $\varnothing$ d <sub>1</sub>	40 mm
Suitable toggle spanner No. 309840	40
External $\varnothing$ D	89 mm
Clamping $\varnothing$ D <sub>1</sub>	40 mm

Adapter	PSC 80 short
Arbor standard	ISO 26623-1
Cooling channel bore	lockable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Type of product	Milling head arbor

---

## Accessories

Toggle spanner for mandrel Ø 40 mm	309840 40
------------------------------------	-----------