

**Aluminium Oxide (A) finishing belt KK711T, 13×610 mm, Grit: 40****Order data**

| | |
|--------------|---------------|
| Order number | 558010 40 |
| GTIN | 4018875025918 |
| Item class | 56V |

Description**Version:**

Universal finishing belt with **Aluminium Oxide(A)**. The grinding medium underlay is optimally designed to the grit and type of finishing belt.

40 grit - X-fabric (robust). 60 to 180 grit - T-fabric (robust-flexible) with **special flexibility**. Ideal for use on hand-held grinding machines.

Application:

For universal use on all popular materials: **steel**, non-ferrous metals, cast iron, **aluminium alloys**, **wood**.

Note:

Other grit sizes, qualities, and dimensions are available on request in line with the manufacturer's minimum order quantities. Unless specified otherwise on the order, belts will be supplied with standard joints. See No. 568526ff for spare finishing belts for burnishing machines.

Technical description

| | |
|----------------|------------------------------|
| Grit | 40 |
| Series | KK711T |
| Grinding media | Standard aluminium oxide (A) |

| | |
|---|----------------|
| Grinding medium code | A |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Linishing belt width | 13 mm |
| Linishing belt length | 610 mm |
| Product name attribute | 13×610 mm |
| Type of product | Linishing belt |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | 35-40 m/s | |
| Steel < 900 N/mm ² | suitable | 32-38 m/s | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 20-25 m/s | P |
| Steel < 55 HRC | suitable only under restricted conditions | 32-38 m/s | H |
| INOX | suitable only under restricted conditions | 18-30 m/s | |
| Ti | suitable only under restricted conditions | 10-20 m/s | |
| GG(G) | suitable only under restricted conditions | 30-45 m/s | K |
| CuZn | suitable | 35-45 m/s | N |
| Plastic, GRP | suitable | 10-30 m/s | |
| Wood | suitable | 23-26 m/s | |
| dry | suitable | | |