

**Garant**
**Jobber drill, long, HSS-E N, uncoated, Ø DC h8: 5,8mm**

**Order data**

Order number	116065 5,8
GTIN	4045197270641
Item class	11B

**Description**
**Version:**

Profile ground. Standard core thickness and core taper. Bright finish.  
With point geometry shape AC from 2 mm.

**Advantage:**

For drilling with drill bushes or long reach applications.  
For high-tensile tempered steels, **including TOOLOX.**

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

**Note:**

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability

**Technical description**

Number of cutting edges Z	2
Feed f in steel < 1100 N/mm <sup>2</sup>	0.05 mm/rev.
Nominal Ø D <sub>c</sub>	5.8 mm
Flute length L <sub>c</sub>	91 mm
Tolerance nominal Ø	h8
Shank Ø D <sub>s</sub>	5.8 mm
Overall length L	139 mm
Standard	DIN 340
recommended maximum drilling depth L <sub>2</sub>	82.3 mm

Point angle	118 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS E
Type	N
Helix angle	35-40 degrees
Through-coolant	no
Colour ring	red
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	10 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	8 m/min	P
TOOLOX 33	suitable	8 m/min	H
TOOLOX 44	suitable	5 m/min	H
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	12 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	M
CuZn	suitable only under restricted conditions	80 m/min	N
Oil	suitable		
wet maximum	suitable		