

## Garant

### Deep hole drill HSS-E, TiAlN, Ø DC h8: 7,5mm



#### Order data

Order number	116063 7,5
GTIN	4045197871343
Item class	11B

#### Description

##### Version:

Significantly **strengthened core** without taper.

Precision ground point.

With **specialty shaped slots**. Designed for deep holes up to 10×D and materials with critical chip formation characteristics.

With **TiAlN coating** for long tool lives.

##### Recommendation:

##### Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

##### Note:

Suitable NC spotting drills No. 112120, 112140 and 112170 with **142° tip angle** for enhanced process reliability

#### Technical description

Flute length $L_c$	102 mm
Feed $f$ in steel $< 750 \text{ N/mm}^2$	0.08 mm/rev.
Nominal $\varnothing D_c$	7.5 mm
Shank $\varnothing D_s$	7.5 mm
recommended maximum drilling depth $L_2$	90.8 mm
Standard	DIN 340
Overall length $L$	156 mm
Tolerance nominal $\varnothing$	h8
Number of cutting edges $Z$	2

Point angle	130 degrees
Shank	Plain shank
Coating	TiAlN
Tool material	HSS E
Type	FS
Helix angle	38 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions	87 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	56 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	31 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	23 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	20 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	P
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	6 m/min	S
GG(G)	suitable	31 m/min	K
Oil	suitable		
wet maximum	suitable		