

Garant
Solid carbide ball nose roughing end mill, TiAlN, Ø d11 DC: 12mm


Order data

Order number	207505 12
GTIN	4045197882752
Item class	11X

Description

Version:

Round **knuckle form profile** for roughing, **including machining radii.**

Note:

Successor product to No. 207512

Technical description

Feed f_z for copy milling in steel $< 900 \text{ N/mm}^2$	0.09 mm
Shank $\varnothing D_s$	12 mm
No. of teeth Z	3
Overall length L	73 mm
Cutting edge $\varnothing D_c$	12 mm
Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.08 mm
Flute length L_c	26 mm
Helix angle	45 degrees
Radius R	6 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Milling profile	HR

Tolerance nominal \varnothing	d11
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.5×D for side milling
Shank	DIN 6535 HB to h6
Through-coolant	no
Colour ring	without
Type of product	Ball-nosed slot drill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	350 m/min	N
Alu > 10% Si	suitable only under restricted conditions	250 m/min	N
Steel < 500 N/mm ²	suitable	160 m/min	P
Steel < 750 N/mm ²	suitable	140 m/min	P
Steel < 900 N/mm ²	suitable	130 m/min	P
Steel < 1100 N/mm ²	suitable	80 m/min	P
INOX < 900 N/mm ²	suitable	80 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

