



Abrasive flap disc V2 Power, (ZA), flat-dished for steel, 125 mm Ø, Grit: 60



Order data

| | |
|--------------|---------------|
| Order number | 565462 60 |
| GTIN | 4027497408948 |
| Item class | 53L |

Description

Version:

The patented sickle-shaped strip-form and configuration permit a high coating density for an exceptional metal removal rate and a long tool life.

Glass fibre plate for **general-purpose use**.

Pure **Zirconium Aluminium Oxide** on a polyester-cotton mixed fabric. Very aggressive due to the open grit distribution.

Application:

Low-vibration working and long working life.

Note:

Padless flap discs SLTflex for gentle cutting, fillet weld smoothing etc. can be found under No. 566300 ff.

Technical description

| | |
|-------------------|-------------|
| Shape description | flat-dished |
| Grit | 60 |
| Bore Ø | 22.23 mm |

| | |
|---|--------------------|
| Disc Ø | 125 mm |
| Grinding medium code | ZA |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | 125 mm Ø |
| Backing pad | Glass fibre pad |
| optimised for material | Steel |
| maximum circumferential speed | 80 m/s |
| Type of product | Abrasive flap disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable only under restricted conditions | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| dry | suitable | | |