



## Knife file cut 3 (smooth), Length without tang: 200mm



### Order data

Order number	518100 200
GTIN	4009215074833
Item class	56B

### Description

#### Version:

The blanks are forged and ground; manufactured with an exact cut of even density and depth using special machines. The finished files have an ideal tooth profile for each type of file. These special files guarantee smooth filed surface finishes. **Special files** are manufactured on precision automated machines. They **guarantee a high removal rate and long tool-life.**

**Cuts on all faces; plain end.**

### Technical description

Cross section	20×6.4 mm
Length without tang	200 mm
Shape	G
Standard	DIN 7262
Type of product	Knife file

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		

Steel < 60 HRC	suitable only under restricted conditions
INOX	suitable only under restricted conditions
GG(G)	suitable
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable only under restricted conditions

## Accessories

Plastic file handle Overall length 100 mm	519510 100
2-component ergonomic file handle Overall length 120 mm	519600 120
Hardwood file handle Overall length 120 mm	519400 120
File brush Bristle length L3× width L1 80X20 mm	576000 80X20
Plastic file handle Overall length 110 mm	519550 110
Plastic file handle Overall length 110 mm	519510 110
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
File brush Bristle length L3× width L1 100X25 mm	576000 100X25
2-component ergonomic file handle Overall length 110 mm	519600 110