

## Milled file, flat plain medium, fine, Length without tang: 300mm



### Order data

Order number	519130 300
GTIN	2050001696250
Item class	56B

### Description

#### Version:

**Milled files** are characterised by the special **sharpness** of their teeth milled out of the solid with optimum chip grooves. This allows filings from soft and clogging materials to be cleared reliably.

**Will not clog.**

**Parallel flat, milled on 3 sides.**

### Technical description

Length without tang	300 mm
Cross section	31×7 mm
Grit designation	fine
Tooth spacing approx.	1.5 mm
Shape	A
Product name attribute	fine
Standard	DIN 7264
for material	Stainless steels, hard materials, synthetic resins, sheet metal. Suitable for edge breaking, honing, fine dressing.
Type of product	Milled file

### User data

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions		
Steel < 55 HRC	suitable only under restricted conditions		
INOX	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		

## Accessories

Plastic file handle Overall length 120 mm	519550 120
File brush Bristle length L3× width L1 100X25 mm	576000 100X25
Hardwood file handle Overall length 160 mm	519400 160
2-component ergonomic file handle Overall length 120 mm	519600 120
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
File brush Bristle length L3× width L1 80X20 mm	576000 80X20
Plastic file handle Overall length 125 mm	519510 125