

Garant**Burr Z9 – very coarse (non-ferrous / aluminium), Carbide, Type: F1630****Order data**

Order number	543709 F1630
GTIN	4045197522429
Item class	51D

Description**Version:**

Extra sturdy shank with \varnothing 8 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Round arch shape** (RBF).

Application:

For the most demanding burring operations.

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape description	round arch
Toothing grit designation	very coarse (NF/Alu)
Overall length	70 mm
Shape	F1630
Tooth type abbreviation	Z9
Head \varnothing	16 mm
Shank \varnothing	8 mm
Head length	30 mm
Series	Tooth configuration Z9

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		