



V4 Master flap disc (ZA) glass fibre plate, dished for steel and stainless steels, 125 mm Ø, Grit: 40



Order data

Order number	565445 40
GTIN	4027497469963
Item class	53L

Description

Version:

The patented sickle-shaped strip-form and configuration permit a high coating density for an exceptional metal removal rate and a long tool life.

High coating density for a very long working life and **outstanding edge stability**. The deep depression permits optimum exploitation of the abrasive fabric (ZA).

ZA: Pure **Zirconium Aluminium Oxide** on a polyester-cotton mixed fabric. Very aggressive due to the open grit distribution.

Application:

Ideal for **edge grinding** on high-power machines, for **rounding sharp edges**, dressing weld seams and removing weld slag residues.

Technical description

Shape description	dished
Bore Ø	22.23 mm
Grit	40

Disc Ø	125 mm
Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	125 mm Ø
optimised for material	Steel
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
dry	suitable		