

HOLEX®
Flap disc (ZA) glass fibre pad flat, 115 mm Ø, Grit: 40
Order data

Order number	565700 40
GTIN	4045197157881
Item class	52M

Description
Version:

Roughing grinding discs with cloth flaps coating with Zirconium Aluminium Oxide (ZA) or ceramic grit on backing pads of steel, plastic or glass fibre. Circumferential speed **ideally 50-60 m/s**, max. 80 m/s. Gentle, cool grinding with high self-sharpening effect (no clogging); low vibration and low force working, low noise level.

· **Flat shape – for surface grinding – and weld dressing with approach angles 0 -15°.**

Flap disc with glass fibre pad and mixed fabric with high metal removal rate and long service life.

Application:

Universal for **all steels**, preferably for use on **flat surfaces**.

Grinding medium code: ZA

Iron, sulphur and chlorine constituents: < 0.1 %

optimised for material: Steel

optimised for material: INOX

maximum circumferential speed: 80 m/s

Shape description: flat

Bore Ø: 22.23 mm

Technical description

Bonding	
Grinding media	
abrasive, cooling coating	
Grit structure	
Adapter	
Shape	
recommended circumferential speed	m/s

Thread	
Grinding medium code	ZA
Grinding media backing	
recommended approach angle	degrees
See-through grinding	
Backing pad	
optimised for material	Steel
optimised for material	INOX
Propulsive equipment	
Iron, sulphur and chlorine constituents	< 0.1 %
suitable for quick-change system	
maximum circumferential speed	80 m/s
Product name attribute	115 mm Ø
maximum speed	rpm
Type of product	