



Linishing belt ceramic grit XK870X, 150×2000 mm, Grit: 60



Order data

Order number	558430 60
GTIN	4018875351147
Item class	56V

Description

Version:

XK870 linishing belt with self-sharpening **ceramic grit (CER)** for very high performance and long service life. The active abrasive layer (**TOP Size**) ensures cool abrasion and increases the material removal rate.

X-fabric (robust) for linishing work on **stationary linishing machines** with high contact forces.

Application:

For grinding all steels, particularly well suited to difficult to machine materials such as **stainless steel, nickel alloys, chromium**, titanium, aluminium.

Note:

Other grit sizes, qualities, and dimensions are available on request in line with the manufacturer's minimum order quantities. Unless specified otherwise on the order, belts will be supplied with standard joints. See No. 568526ff for spare linishing belts for burnishing machines.

Technical description

Grit	60
Series	XK870X
Grinding media	Ceramic grit

Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	150 mm
Linishing belt length	2000 mm
Product name attribute	150×2000 mm
Type of product	Linishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions	35-40 m/s	
Steel < 900 N/mm ²	suitable	32-38 m/s	P
Steel < 1400 N/mm ²	suitable	20-25 m/s	P
Steel < 55 HRC	suitable	32-38 m/s	H
Steel < 60 HRC	suitable	25-30 m/s	H
Steel < 67 HRC	suitable	20-25 m/s	H
INOX	suitable	18-30 m/s	
Ti	suitable only under restricted conditions	10-20 m/s	
GG(G)	suitable	30-45 m/s	K
CuZn	suitable only under restricted conditions	35-45 m/s	N
Uni	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		