

Garant**Burr Z7 – medium, diamond cut, Carbide, Type: D1210****Order data**

Order number	543200 D1210
GTIN	4045197609861
Item class	51D

Description**Version:**

Extra sturdy shank with Ø 8 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Ball shape** (KUD)

Application:

For the most demanding burring operations.

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Shape	Ball shape
Tooth type abbreviation	Z7
Head Ø	12 mm
Overall length	50 mm

Shape description	ball
Toothing grit designation	medium
Type of cut	staggered teeth
Shank Ø	8 mm
Head length	10 mm
Series	Tooth configuration Z7
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		