



Burr Tooth configuration STEEL – coarse, Carbide, Type: L1230



Order data

Order number	547100 L1230
GTIN	4007220936818
Item class	55F

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Shank \varnothing : 6 mm

Shape description: round cone

Head \varnothing : 12 mm

Head length: 30 mm

Overall length: 70 mm

Shank \varnothing : 6 mm

Technical description

Tooth type abbreviation	STEEL
Shape description	round cone
Overall length	70 mm
Head \varnothing	12 mm
Shape	L1230
Toothing grit designation	coarse
Shank \varnothing	6 mm
Head length	30 mm

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		