

**Garant**
**Jobber drill long HSS N, uncoated, Ø DC h8: 3,2mm**

**Order data**

Order number	116000 3,2
GTIN	4045197025340
Item class	11B

**Description**
**Version:**

Vaporised from 2.4 mm. Particularly for deep hole drilling (for deep holes, repeated chip evacuation is necessary).

With point geometry shape A from size 4 mm.

**Advantage:**

Especially suitable for **long reach purposes**. (When used to drill deep holes, low feed rates and frequent drill pecks are necessary).

**Recommendation:**
**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c$$

**Note:**

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability.

**Technical description**

Number of cutting edges Z	2
Flute length $L_c$	69 mm
Nominal $\varnothing D_c$	3.2 mm
Feed f in steel < 750 N/mm <sup>2</sup>	0.02 mm/rev.
Tolerance nominal $\varnothing$	h8
Shank $\varnothing D_s$	3.2 mm
Overall length L	106 mm
Standard	DIN 340

recommended maximum drilling depth $L_2$	64.2 mm
Point angle	118 degrees
Shank	Plain shank
Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

### User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	64 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	52 m/min	N
Alu > 10% Si	suitable only under restricted conditions	40 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	40 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		