

HOLEX**Flap wheel (A), 40 grit, Head Ø×head width: 40X20mm****Order data**

| | |
|--------------|---------------|
| Order number | 554095 40X20 |
| GTIN | 4045197526816 |
| Item class | 52E |

Description**Version:**

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **regular Aluminium Oxide (A)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

| | |
|-------------------|-------------------------|
| Grit | 40 |
| maximum speed | 19100 min ⁻¹ |
| recommended speed | 12000 min ⁻¹ |
| Head width | 20 mm |
| Shank Ø | 6 mm |
| Head Ø | 40 mm |

| | |
|------------------------|--------------------------|
| Grinding media | Aluminium Oxide grit (A) |
| Grinding medium code | A |
| Product name attribute | 40 grit |
| Type of product | Flap wheel |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable only under restricted conditions | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| dry | suitable | | |