



LED machine lamp flat, Type: 305 mm



Order data

Order number	081436 305
GTIN	4260131236068
Item class	08C

Description

Version:

Sturdy LED machine lamps in an **aluminium casing**, with a satinised acrylic lens for **homogeneous 160-degree illumination**.

- **Low-reflection, non-dazzle and non-flicker.**
- **For connection to a 24 V mains adapter or 24 V machine control system.**

Supplied with:

With 2× rubber-clad magnets, mains adapter.

IP Index of Protection: IP 67

Light output: 12 W

Illumination: 1200 lm

Energy efficiency class : A

Overall width: 40 mm

Overall height: 15 mm

Technical description

Light output	12 W
Illumination	1200 lm
Bulb	LED module
Energy efficiency class	A
Overall height	15 mm

ATEX zone	no
Overall width	40 mm
IP Index of Protection	IP 67