

Garant**Flap disc Fleece, Ø 125 mm, Grit equivalent: 100****Order data**

Order number	566340 100
GTIN	4045197488886
Item class	56Z

Description**Version:**

Fleece flap discs with **flaps of abrasive fleece** on a glass fibre pad.

Application:

- **For final finishing of surfaces.**
- **For removal of colouration, cleaning, and minor tidying up of weld seams.**
- **For fine grinding of large areas and for finishing.**

Recommended speed 4600 – 5300 rpm.

Technical description

Bore Ø	22.23 mm
Colour	brown
Grit equivalent	100
Grit designation	coarse
Shape description	dished
Disc Ø	125 mm
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	INOX
maximum circumferential speed	80 m/s
maximum speed	12200 min ⁻¹
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		