



## Burr Tooth configuration STEEL – coarse, Carbide, Type: C1020



### Order data

Order number	547100 C1020
GTIN	4007220937174
Item class	55F

### Description

#### Version:

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

#### Application:

Optimised for **use on steel and steel castings**.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 10 mm

Head length: 20 mm

Overall length: 60 mm

Shank Ø: 6 mm

### Technical description

Shape	C1020
Head Ø	10 mm
Overall length	60 mm
Shape description	ball nose
Tooth type abbreviation	STEEL
Toothing grit designation	coarse
Shank Ø	6 mm
Head length	20 mm

Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		