



## Burr Tooth configuration STEEL – coarse, Carbide, Type: C1225



### Order data

Order number	547100 C1225
GTIN	4007220936696
Item class	55F

### Description

#### Version:

**The innovative tooth geometry** permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank Ø 6 mm.

#### Application:

Optimised for **use on steel and steel castings**.

Shank Ø: 6 mm

Shape description: ball nose

Head Ø: 12 mm

Head length: 25 mm

Overall length: 65 mm

Shank Ø: 6 mm

### Technical description

Overall length	65 mm
Head Ø	12 mm
Shape	C1225
Tooth type abbreviation	STEEL
Toothing grit designation	coarse
Shape description	ball nose
Shank Ø	6 mm
Head length	25 mm

Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		