

FLUKE.

**Multimeter, Type: 179****Order data**

Order number	473322 179
GTIN	095969095860
Item class	47H

**Description****Version:**

Ergonomic plastic housing with integral holster. Large LCD display for good legibility. Reliable and easy to use – **warning if the test leads are connected wrongly**. The leading measuring tools for troubleshooting electrical and electronic systems for professional technicians. Robust, reliable and precise.

Additional LED backlight and temperature measurement.

**Application:**

Digital service multimeters for a wide range of applications, very high safety and other additional functions.

**Standard:**

**IEC 61010; ANSI/ISA S82.02.01; CSA C22.2-1010.1**

**Supplied with:**

Battery 081561 6LR61, test leads, and removable insulating caps. Temperature sensor.

**Technical description**

Basic accuracy	0.09 %
AC current	0.1 mA – 10 A

Diode testing	yes
Measurement process	TRUE RMS
Calibration	I3
Calibration	I7
Continuity testing	yes
Display backlit	yes
Capacitance	1 nF – 10 mF
Information displayed	6000
DC current	0.1 mA – 10 A
Overvoltage category	CAT III 1000 V
Overvoltage category	CAT IV 600 V
AC voltage	0.1 mV – 1000 V
Frequency	0.01 Hz – 100 kHz
Temperature	-40 - 400 °C
Resistance	0.1 Ω – 50 MΩ
DC voltage	0.1 mV – 1000 V
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Type of product	Multimeter

## Services

CalibrationDigital multimeter Number of decimal places 3	027000 3
CalibrationTemperature sensor with / without display Type A	027520 A
DAkKS calibrationDigital multimeter Number of decimal places 3	027010 3
DAkKS calibrationTemperature sensor with / without display Type A	027540 A

## Accessories

Test leads Measuring tips Ø 1 mm	473318 1
Test leads Measuring tips Ø 2 mm	473318 2
Carrying case C150 Type F	473337 F
Magnetic meter hanger Type TPAK	473329 TPAK