



Hook turning tool right-hand, similar to DIN 263 (ISO 11), P20/K25, Shank square: 10mm



Order data

Order number	297135 10
GTIN	4045197885586
Item class	22E

Description

Version:

Carbide – steel shanks with 700 - 800 N/mm² strength and flat chamfered mounting surface. Fitted with diamond ground carbide inserts. Angles on the inserts are precision ground. All turning tools are supplied with sharp cutting edges. Sharpening the cutting edge with a boron carbide hand lapper will increase the tool edge life. The extent of the wear area is dependent on the cutting conditions. For roughing and interrupted machining it is imperative that the cutting edges are sharpened.

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

maximum grooving depth t_{max}	6 mm
Blade width	3 mm
for bores from \varnothing	25 mm
Shank square	10 mm
Overall length	150 mm
Tool material	P20/K25

Type of product

Turning tool