

**HOLEX****Turning tool right-hand, similar to DIN 4980 (ISO 6), M20, Shank square: 25mm****Order data**

Order number	296830 25
GTIN	4045197885524
Item class	22E

**Description****Version:**

Fitted with diamond ground carbide inserts.

**Application:**

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

**Attention:**

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

**Technical description**

Shank square	25 mm
Overall length	140 mm
Tool material	M20
Type of product	Turning tool