



## Hook turning tool right-hand, similar to DIN 263 (ISO 11), M20, Shank square: 12mm



### Order data

Order number	297145 12
GTIN	4045197885609
Item class	22E

### Description

#### Version:

Fitted with diamond ground carbide inserts.

#### Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

#### Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Overall length: 160 mm

Blade width: 4 mm

for bores from  $\varnothing$ : 30 mm

maximum grooving depth  $t_{max}$ : 10 mm

### Technical description

Shank square	12 mm
for bores from $\varnothing$	30 mm
Blade width	4 mm
maximum grooving depth $t_{max}$	10 mm
Overall length	160 mm
Tool material	M20
Type of product	Turning tool

