

HOLEX

Grooving tool right-hand, similar to DIN 4981 (ISO 7), M20, Shank height: 16mm



Order data

Order number	297030 16
GTIN	4045197885548
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Shank height h	16 mm
Blade width	4 mm
Overall length	110 mm
Shank width b	10 mm
Tool material	M20
Type of product	Turning tool